

Bantam[®]

4F Peripheral Catheter 0.018" OTW



FEATURING 6 FOLD ON 7-9.0mm



Now features
QuadFlex[®] Balloon
Material and SiLX[®]
Coating

Part Numbers

	Balloon Diameter	20mm	40mm	60mm	80mm	100mm	120mm	150mm	220mm
Catheter Length 75cm	2.0	48402020	48404020	48406020	48408020	48410020	48412020	48415020	48422020
	2.5	48402025	48404025	48406025	48408025	48410025	48412025	48415025	48422025
	3.0	48402030	48404030	48406030	48408030	48410030	48412030	48415030	48422030
	3.5	48402035	48404035	48406035	48408035	48410035	48412035	48415035	48422035
	4.0	48402040	48404040	48406040	48408040	48410040	48412040	48415040	48422040
	5.0	48402050	48404050	48406050	48408050	48410050	48412050	48415050	48422050
	6.0	48402060	48404060	48406060	48408060	48410060	48412060	48415060	48422060
	7.0		48404070	48406070					
	8.0		48404080	48406080					
9.0		48404090	48406090						

	Balloon Diameter	20mm	40mm	60mm	80mm	100mm	120mm	150mm	220mm
Catheter Length 90cm	2.0		48804020		48808020		48812020		
	2.5		48804025		48808025		48812025		
	3.0		48804030		48808030		48812030		

	Balloon Diameter	20mm	40mm	60mm	80mm	100mm	120mm	150mm	220mm
Catheter Length 130cm	2.0	48502020	48504020	48506020	48508020	48510020	48512020	48515020	48522020
	2.5	48502025	48504025	48506025	48508025	48510025	48512025	48515025	48522025
	3.0	48502030	48504030	48506030	48508030	48510030	48512030	48515030	48522030
	3.5	48502035	48504035	48506035	48508035	48510035	48512035	48515035	48522035
	4.0	48502040	48504040	48506040	48508040	48510040	48512040	48515040	48522040
	5.0	48502050	48504050	48506050	48508050	48510050	48512050	48515050	48522050
	6.0	48502060	48504060	48506060	48508060	48510060	48512060	48515060	48522060
	7.0		48504070	48506070					
	8.0		48504080	48506080					
9.0		48504090	48506090						

Product Specification

Balloon				
Average compliance	8%			
Catheter Length	75cm, 90cm & 130cm			
Nominal pressure	6Atm			
Rated Pressure	Balloon Diameter	20-60mm	80-220mm	
	2.0-4.0mm	16Atm	15Atm	
	5.0mm	14Atm	13Atm	
	6.0mm	14Atm	12Atm	
	7.0-8.0mm	12Atm		
	9.0mm	11Atm		
	Average burst pressure	Balloon Diameter	20-60mm	80-220mm
		2.0-4.0mm	22Atm	21Atm
		5.0mm	20Atm	19Atm
6.0mm		19Atm	17Atm	
7.0 & 8.0mm		16Atm		
9.0mm		15Atm		
Marker Bands	Swaged 1.0mm Platinum/Iridium marker bands delineates the working surface			
Guide Wire	0.018"			
Tip Lead-in Profile	<0.021"			
Sheath Compatibility	Balloon Diameter			
	2.0-5.0mm	4F		
	6.0-7.0mm	5F		
	8.0-9.0mm	6F		
Fold	Balloon Diameter			
	2.0mm	Bifold		
	2.5-6.0mm	Trifold		
	7.0-9.0mm	Sixfold		
Coating	SiLX coating for maximum lubricity			

clearStream

Technologies Ltd

Moyne Upper, Enniscorthy, Co. Wexford, Ireland.
 Tel: +353 (0)53 9237111 Fax: +353 (0)53 9237100
 E: info@clearstream.ie W: www.clearstream.ie

INS 012, Rev. 1.1